




INSULATING GLOVES JAPAREX LINE

■ HIGH VOLTAGE RUBBER INSULATING GLOVES



ITEM NO.	SIZE	A.C. PROOF TEST VOLTAGE	A.C. MAXIMUM USE VOLTAGE	LENGTH
YS-101-32-04	LL	30kV/3min	26.5kV	460mm
YS-101-32-03	L			
YS-101-32-02	M			
YS-101-31-04	LL	20kV/3min	17kV	460mm
YS-101-31-03	L			
YS-101-31-02	M			
YS-101-90-04	LL	20kV/3min	17kV	380mm
YS-101-90-03	L			
YS-101-90-02	M			
YS-101-20-01	LL	20kV/1min	7kV	460mm
YS-101-21-01	L			
YS-101-22-01	M			
YS-101-20-03	LL	20kV/1min	7kV	380mm
YS-101-21-03	L			
YS-101-22-03	M			

The RUBBER INSULATING GLOVES are used for protection of electrical workers from electrical shock. The RUBBER INSULATING GLOVES are most important personal protective equipment. We take carefully quality control to ensure using safety condition.

絕緣手套的使用是用於保護電氣作業人員防止電擊。橡膠絕緣手套是非常重要的個人安全保護用品。每一隻手套在出廠之前都經過我們嚴格的品質檢驗，以確保使用的安全。

■ PROTECTIVE GLOVES



TYPE. M



TYPE. F

ITEM NO.	SIZE	A.C. PROOF TEST VOLTAGE	A.C. MAXIMUM USE VOLTAGE	TYPE
YS-103-12-02	FREE	/	/	F
YS-103-13-02	L	/	/	M
YS-103-13-04	S	/	/	M

The PROTECTIVE GLOVES are recommended to be used for preventing RUBBER INSULATING GLOVES from physical and mechanical damages, over the rubber gloves.

保護手套是用於穿戴於橡膠絕緣手套外，用以保護絕緣手套不受物理及機械傷害。



INSULATING GLOVES JAPAREX LINE

■ LOW VOLTAGE RUBBER INSULATING GLOVES



ITEM NO.	SIZE	A.C. PROOF TEST VOLTAGE	A.C. MAXIMUM USE VOLTAGE	LENGTH
YS-102-04-00	LL	3kV/1min	600V	280mm
YS-102-01-00	L			270mm
YS-102-02-00	M			270mm
YS-102-13-04	LL	5kV/3min	1kV	280mm
YS-102-13-03	L			270mm
YS-102-13-02	M			270mm

■ LOW VOLTAGE RUBBER INSULATING GLOVES(DOUBLE LAMINATION)



ITEM NO.	SIZE	A.C. PROOF TEST VOLTAGE	A.C. MAXIMUM USE VOLTAGE	LENGTH
YS-102-10-01	LL	3kV/1min	600V	270mm
YS-102-11-01	L			
YS-102-12-01	M			



STORAGE CONDITION OF RUBBER INSULATING GLOVES

推薦絕緣天然橡膠手套儲存方法

We pay a special attention on manufacturing the insulating gloves to keep them long life. but, please pay your attention on the following points while you store and keep them after using, and they will maintain much longer.

1. Proper Storage Condition

- (1) stored in initial boxes right side out and not folded.
- (2) stored away from the direct sunlight, steam pipes, radiators, and other excessive heat (It is desirable that the ambient storage temperature shall not exceed 35°C).
- (3) stored in a location where ozone is not present.

2. After Use

In the case of storage, please remove water completely, throw talc powder all over the surface, put them in the initial carton without any folding, and keep them in a dry, cool and dark place.

良好的絕緣手套的保養及儲放方法可以保存手套品質及使用壽命。

A. 絕緣手套儲存方法:

1. 儲放在原始的包裝盒內, 不可以摺疊。
2. 避免直接太陽照射, 或將手套儲放在蒸氣管, 散熱器或是其他加熱裝置附近。儲存溫度不要超過35°C
3. 避免放在有臭氧的地方。

B. 手套使用後的清潔及保養:

手套使用後應以清水清洗之後 平放晾乾 等手套全乾之後在手套外部灑上石磨粉以保持乾燥, 然後平放在包裝盒內並儲存於乾燥陰涼的地方。



YOTSUGI CO.,LTD.

Tokyo Office : 2-6-13, Kyobashi, Chuo-ku, Tokyo, Japan.

〒104-0031

TEL : (81) 3-3563-5616

FAX : (81) 3-3535-0789

URL: <http://www.yotsugi.co.jp>